
AttaBox Series Polycarbonate Enclosures

Opaque Door with Polycarbonate Quick-release Latch Latches, Mounting Feet

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH12106



Construction

- Polycarbonate with UV inhibitors
- Robotically-applied foam-in-place polyurethane seamless gasket
- 304 stainless steel cover screws
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24in·lb cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Polycarbonate with UV inhibitors hinge and latch hardware
- Variable depth side mount capability
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Sliding T-Nut allows for infinite panel adjustment back to front
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Aluminum back panel and swing-out panel mounting options
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

c UL us CE

AttaBox Series Polycarbonate Enclosures – Opaque Door with Polycarbonate Quick-release Latch Latches, Mounting Feet

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AH664	$91.00	6.00 x 6.00 x 4.00 [152 x 152 x 102]	PDF	BP66AL	$13.00	BP66ABS	$17.00
AH864	$97.00	8.00 x 6.00 x 4.00 [203 x 152 x 102]	PDF	BP86AL	$15.50	BP86ABS	$18.00
AH884	$101.00	8.00 x 8.00 x 4.00 [203 x 203 x 102]	PDF	BP88AL	$20.50	—	
AH1084	$118.00	10.00 x 8.00 x 4.00 [254 x 203 x 102]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH1086	$123.00	10.00 x 8.00 x 6.00 [254 x 203 x 152]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH10106	$130.00	10.00 x 10.00 x 6.00 [254 x 254 x 152]	PDF	BP1010AL	$28.00	BP1010ABS	$23.50
AH12106	$163.00	12.00 x 10.00 x 6.00 [305 x 254 x 152]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AH14126	$192.00	14.00 x 12.00 x 6.00 [356 x 305 x 152]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AH16148	$217.00	16.00 x 14.00 x 8.00 [406 x 356 x 203]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AH181610	$256.00	18.00 x 16.00 x 10.00 [457 x 406 x 254]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AH20168	$375.00	20.00 x 16.00 x 8.00 [508 x 406 x 203]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00
AH242410*	$672.00	24.00 x 24.00 x 10.00 [610 x 610 x 254]	PDF	BP2424PCAL	$106.00	BP2424ABS	$66.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox Series Polycarbonate Enclosures

Smoked Door with Polycarbonate Quick-release Latch Latches, Mounting Feet

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH12106C



Construction

- Polycarbonate with UV inhibitors
- Neoprene rope style gasket
- Poured polyurethane seamless gasket in select sizes
- Includes polycarbonate mounting feet kit
- 304 stainless steel cover screw
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24 in·lb cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Polycarbonate with UV inhibitors hinge and latch hardware
- Variable depth side mount capability
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Sliding T-Nut allows for infinite panel adjustment back to front
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Aluminum back panel and swing-out panel mounting options
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

c UL us CE

AttaBox Series Polycarbonate Enclosures – Smoked Door with Polycarbonate Quick-release Latch Latches, Mounting Feet

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AH664C	$99.00	6.00 x 6.00 x 4.00 [152 x 152 x 102]	PDF	BP66AL	$13.00	BP66ABS	$17.00
AH864C	$109.00	8.00 x 6.00 x 4.00 [203 x 152 x 102]	PDF	BP86AL	$15.50	BP86ABS	$18.00
AH884C	$116.00	8.00 x 8.00 x 4.00 [203 x 203 x 102]	PDF	BP88AL	$20.50	—	
AH1084C	$139.00	10.00 x 8.00 x 4.00 [254 x 203 x 102]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH1086C	$144.00	10.00 x 8.00 x 6.00 [254 x 203 x 152]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH10106C	$152.00	10.00 x 10.00 x 6.00 [254 x 254 x 152]	PDF	BP1010AL	$28.00	BP1010ABS	$23.50
AH12106C	$182.00	12.00 x 10.00 x 6.00 [305 x 254 x 152]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AH14126C	$201.00	14.00 x 12.00 x 6.00 [356 x 305 x 152]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AH16148C	$246.00	16.00 x 14.00 x 8.00 [406 x 356 x 203]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AH181610C	$285.00	18.00 x 16.00 x 10.00 [457 x 406 x 254]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AH20168C	$439.00	20.00 x 16.00 x 8.00 [508 x 406 x 203]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00
AH242410C*	$720.00	24.00 x 24.00 x 10.00 [610 x 610 x 254]	PDF	BP2424PCAL	$106.00	BP2424ABS	$66.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox Series Polycarbonate Enclosures

Opaque Door with Stainless Steel Quick-release Latch Latches, Mounting Feet

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH12106SS



Construction

- Polycarbonate with UV inhibitors
- Neoprene rope style gasket
- Poured polyurethane seamless gasket in select sizes
- Includes polycarbonate mounting feet kit
- 316 stainless steel cover screws and latches
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size - #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24 in·lb cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Variable depth side mount capability
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

AttaBox Series Polycarbonate Enclosures – Opaque Door with Stainless Steel Quick-release Latch Latches, Mounting Feet							
Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AH664SS	$98.00	6.00 x 6.00 x 4.00 [152 x 152 x 102]	PDF	BP66AL	$13.00	BP66ABS	$17.00
AH864SS	$104.00	8.00 x 6.00 x 4.00 [203 x 152 x 102]	PDF	BP86AL	$15.50	BP86ABS	$18.00
AH884SS	$109.00	8.00 x 8.00 x 4.00 [203 x 203 x 102]	PDF	BP88AL	$20.50	—	
AH1084SS	$127.00	10.00 x 8.00 x 4.00 [254 x 203 x 102]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH1086SS	$132.00	10.00 x 8.00 x 6.00 [254 x 203 x 152]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH10106SS	$139.00	10.00 x 10.00 x 6.00 [254 x 254 x 152]	PDF	BP1010AL	$28.00	BP1010ABS	$23.50
AH12106SS	$176.00	12.00 x 10.00 x 6.00 [305 x 254 x 152]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AH14126SS	$206.00	14.00 x 12.00 x 6.00 [356 x 305 x 152]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AH16148SS	$233.00	16.00 x 14.00 x 8.00 [406 x 356 x 203]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AH181610SS	$275.00	18.00 x 16.00 x 10.00 [457 x 406 x 254]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AH20168SS	$403.00	20.00 x 16.00 x 8.00 [508 x 406 x 203]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00
AH242410SS*	$722.00	24.00 x 24.00 x 10.00 [610 x 610 x 254]	PDF	BP2424PCAL	$106.00	BP2424ABS	$66.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox Series Polycarbonate Enclosures

Smoked Door with Stainless Steel Quick-release Latch Latches, Mounting Feet

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH12106CSS



Construction

- Polycarbonate with UV inhibitors
- Neoprene rope style gasket
- Poured polyurethane seamless gasket in select sizes
- Includes polycarbonate mounting feet kit
- 316 stainless steel cover screw and latches
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24 in·lb cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Variable depth side mount capability
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Sliding T-Nut allows for infinite panel adjustment back to front
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Aluminum back panel and swing-out panel mounting options
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

AttaBox Series Polycarbonate Enclosures – Smoked Door with Stainless Steel Quick-release Latch Latches, Mounting Feet

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AH664CSS	$106.00	6.00 x 6.00 x 4.00 [152 x 152 x 102]	PDF	BP66AL	$13.00	BP66ABS	$17.00
AH864CSS	$118.00	8.00 x 6.00 x 4.00 [203 x 152 x 102]	PDF	BP86AL	$15.50	BP86ABS	$18.00
AH884CSS	$125.00	8.00 x 8.00 x 4.00 [203 x 203 x 102]	PDF	BP88AL	$20.50	—	
AH1084CSS	$150.00	10.00 x 8.00 x 4.00 [254 x 203 x 102]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH1086CSS	$155.00	10.00 x 8.00 x 6.00 [254 x 203 x 152]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH10106CSS	$163.00	10.00 x 10.00 x 6.00 [254 x 254 x 152]	PDF	BP1010AL	$28.00	BP1010ABS	$23.50
AH12106CSS	$196.00	12.00 x 10.00 x 6.00 [305 x 254 x 152]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AH14126CSS	$216.00	14.00 x 12.00 x 6.00 [356 x 305 x 152]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AH16148CSS	$264.00	16.00 x 14.00 x 8.00 [406 x 356 x 203]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AH181610CSS	$306.00	18.00 x 16.00 x 10.00 [457 x 406 x 254]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AH20168CSS	$472.00	20.00 x 16.00 x 8.00 [508 x 406 x 203]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00
AH242410CSS*	$774.00	24.00 x 24.00 x 10.00 [610 x 610 x 254]	PDF	BP2424PCAL	$106.00	BP2424ABS	$66.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox Series Polycarbonate Enclosures

Opaque Door with Polycarbonate Quick-release Latch Latches, Mounting Flanges

STAHLIN
A ROBROY ENCLOSURES® BRAND



AHF1086



Construction

- Polycarbonate
- Robotically-applied foam-in-place polyurethane seamless gasket
- Includes polycarbonate mounting flange kit
- 304 stainless steel cover screws
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24in·lb cover screw torque
- 1/4-20x1/2 mounting flange inserts
- 10-14 in·lb mounting flange torque
- Polycarbonate with UV inhibitors hinge and latch hardware
- Variable depth side mount capability
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Sliding T-Nut allows for infinite panel adjustment back to front
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Aluminum back panel and swing-out panel mounting options
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

AttaBox Series Polycarbonate Enclosures – Opaque Door with Polycarbonate Quick-release Latch Latches, Mounting Flanges

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AHF664*	$102.00	6.00 x 6.00 x 4.00 [152 x 152 x 102]	PDF	BP66AL	$13.00	BP66ABS	$17.00
AHF864*	$108.00	8.00 x 6.00 x 4.00 [203 x 152 x 102]	PDF	BP86AL	$15.50	BP86ABS	$18.00
AHF884*	$116.00	8.00 x 8.00 x 4.00 [203 x 203 x 102]	PDF	BP88AL	$20.50	—	
AHF1084*	$133.00	10.00 x 8.00 x 4.00 [254 x 203 x 102]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AHF1086*	$138.00	10.00 x 8.00 x 6.00 [254 x 203 x 152]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AHF10106*	$149.00	10.00 x 10.00 x 6.00 [254 x 254 x 152]	PDF	BP1010AL	$28.00	BP1010ABS	$23.50
AHF12106*	$183.00	12.00 x 10.00 x 6.00 [305 x 254 x 152]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AHF14126*	$216.00	14.00 x 12.00 x 6.00 [356 x 305 x 152]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AHF16148*	$245.00	16.00 x 14.00 x 8.00 [406 x 356 x 203]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AHF181610*	$288.00	18.00 x 16.00 x 10.00 [457 x 406 x 254]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AHF20168*	$408.00	20.00 x 16.00 x 8.00 [508 x 406 x 203]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox Series Polycarbonate Enclosures

Smoked Door with Polycarbonate Quick-release Latch Latches, Mounting Flanges

STAHLIN
A ROBROY ENCLOSURES® BRAND



AHF1086C



Construction

- Polycarbonate
- Robotically-applied foam-in-place polyurethane seamless gasket
- Includes polycarbonate mounting flange kit
- 304 stainless steel cover screws
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24in·lb cover screw torque
- 1/4-20x1/2 mounting flange inserts
- 10-14 in·lb mounting flange torque
- Polycarbonate with UV inhibitors hinge and latch hardware
- Variable depth side mount capability
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Sliding T-Nut allows for infinite panel adjustment back to front
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Aluminum back panel and swing-out panel mounting options
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

AttaBox Series Polycarbonate Enclosures – Smoked Door with Polycarbonate Quick-release Latch Latches, Mounting Flanges

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AHF664C*	$109.00	6.00 x 6.00 x 4.00 [152 x 152 x 102]	PDF	BP66AL	$13.00	BP66ABS	$17.00
AHF864C*	$120.00	8.00 x 6.00 x 4.00 [203 x 152 x 102]	PDF	BP86AL	$15.50	BP86ABS	$18.00
AHF884C*	$131.00	8.00 x 8.00 x 4.00 [203 x 203 x 102]	PDF	BP88AL	$20.50	—	
AHF1084C*	$154.00	10.00 x 8.00 x 4.00 [254 x 203 x 102]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AHF1086C*	$159.00	10.00 x 8.00 x 6.00 [254 x 203 x 152]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AHF10106C*	$171.00	10.00 x 10.00 x 6.00 [254 x 254 x 152]	PDF	BP1010AL	$28.00	BP1010ABS	$23.50
AHF12106C*	$202.00	12.00 x 10.00 x 6.00 [305 x 254 x 152]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AHF14126C*	$225.00	14.00 x 12.00 x 6.00 [356 x 305 x 152]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AHF16148C*	$274.00	16.00 x 14.00 x 8.00 [406 x 356 x 203]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AHF181610C*	$317.00	18.00 x 16.00 x 10.00 [457 x 406 x 254]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AHF20168C*	$472.00	20.00 x 16.00 x 8.00 [508 x 406 x 203]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox Series Polycarbonate Enclosures

Opaque Door with Polycarbonate Quick-release Latch Latches, Mounting Feet and Shelf

STAHLIN
A ROBROY ENCLOSURES® BRAND



AHWD12106



Construction

- Polycarbonate
- Robotically-applied foam-in-place polyurethane seamless gasket
- Includes polycarbonate mounting feet kit
- 304 stainless steel cover screws
- Includes internal shelf
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24in·lb cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

AttaBox Series Polycarbonate Enclosures – Opaque Door with Polycarbonate Quick-release Latch Latches, Mounting Feet and Shelf

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AHWD10106	$179.00	10.00 x 10.00 x 6.00 [254 x 254 x 152]	PDF	BP1010AL	$28.00	BP1010ABS	$23.50
AHWD12106	$218.00	12.00 x 10.00 x 6.00 [305 x 254 x 152]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AHWD14126	$251.00	14.00 x 12.00 x 6.00 [356 x 305 x 152]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AHWD16148	$282.00	16.00 x 14.00 x 8.00 [406 x 356 x 203]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AHWD181610	$344.00	18.00 x 16.00 x 10.00 [457 x 406 x 254]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AHWD20168	$445.00	20.00 x 16.00 x 8.00 [508 x 406 x 203]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00
AHWD242410*	$803.00	24.00 x 24.00 x 10.00 [610 x 610 x 254]	PDF	BP2424PCAL	$106.00	BP2424ABS	$66.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox Series Polycarbonate Enclosures

Opaque Door with Mounting Feet, No Latches

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH12106HW



Construction

- Polycarbonate with UV inhibitors
- Robotically-applied foam-in-place polyurethane seamless gasket
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- 304 stainless steel #10-32 x 5/8 cover screws
- 20-24 in·lb cover screw torque
- 1/4-20 x 1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Latches omitted; requires screwdriver for entry
- Fully non-metallic hinge, does not penetrate inside enclosure
- Variable-depth side-mount capability
- Thick, robust sidewall construction eliminates sidewall flexing
- Sliding T-nut allows for infinite panel adjustment back to front
- Optional ABS panel to allow unimpeded transmission of wireless signals
- Aluminum back panel and swing-out panel mounting options
- Temperature range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, 6P, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP68
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

AttaBox Series Polycarbonate Enclosures – Opaque Door with Mounting Feet, No Latches

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AH664HW	$90.00	6.00 x 6.00 x 4.00 [152 x 152 x 102]	PDF	BP66AL	$13.00	BP66ABS	$17.00
AH864HW	$96.00	8.00 x 6.00 x 4.00 [203 x 152 x 102]	PDF	BP86AL	$15.50	BP86ABS	$18.00
AH1084HW	$117.00	10.00 x 8.00 x 4.00 [254 x 203 x 102]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH1086HW	$122.00	10.00 x 8.00 x 6.00 [254 x 203 x 152]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH12106HW	$162.00	12.00 x 10.00 x 6.00 [305 x 254 x 152]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AH14126HW	$190.00	15.00 x 13.00 x 6.00 [381 x 330 x 152]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AH16148HW	$215.00	16.00 x 14.00 x 8.00 [406 x 356 x 203]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AH181610HW	$254.00	18.00 x 16.00 x 10.00 [457 x 406 x 254]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50

Notes: Subpanels must be ordered separately.
Dimensions in in [mm].


AttaBox SL Series Polycarbonate Enclosures

Opaque Door with Polycarbonate Quick-release Latch Latches, Mounting Feet

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH20164



Construction

- Polycarbonate
- Robotically-applied foam-in-place polyurethane seamless gasket
- 304 stainless steel cover screws
- Includes integral mounting feet
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24in·lb cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

AttaBox SL Series Polycarbonate Enclosures – Opaque Door with Polycarbonate Quick-release Latch Latches, Mounting Feet

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AH1083	$112.00	10.00 x 8.00 x 3.00 [254 x 203 x 76]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH12104	$155.00	12.00 x 10.00 x 4.00 [305 x 254 x 102]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AH14124	$182.00	14.00 x 12.00 x 4.00 [356 x 305 x 102]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AH16144	$206.00	16.00 x 14.00 x 4.00 [406 x 356 x 102]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AH18164	$236.00	18.00 x 16.00 x 4.00 [457 x 406 x 102]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AH20164	$359.00	20.00 x 16.00 x 4.00 [508 x 406 x 102]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00
AH24246*	$642.00	24.00 x 24.00 x 6.00 [610 x 610 x 152]	PDF	BP2424PCAL	$106.00	BP2424ABS	$66.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox SL Series Polycarbonate Enclosures

Smoked Door with Polycarbonate Quick-release Latch Latches, Mounting Feet

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH20164C



Construction

- Polycarbonate
- Robotically-applied foam-in-place polyurethane seamless gasket
- 304 stainless steel cover screws
- Includes integral mounting feet
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24in·lb cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Polycarbonate with UV inhibitors hinge and latch hardware
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

AttaBox SL Series Polycarbonate Enclosures – Smoked Door with Polycarbonate Quick-release Latch Latches, Mounting Feet

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AH1083C	$133.00	10.00 x 8.00 x 3.00 [254 x 203 x 76]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH12104C	$174.00	12.00 x 10.00 x 4.00 [305 x 254 x 102]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AH14124C	$192.00	14.00 x 12.00 x 4.00 [356 x 305 x 102]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AH16144C	$235.00	16.00 x 14.00 x 4.00 [406 x 356 x 102]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AH18164C	$276.00	18.00 x 16.00 x 4.00 [457 x 406 x 102]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AH20164C	$420.00	20.00 x 16.00 x 4.00 [508 x 406 x 102]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00
AH24246C*	$688.00	24.00 x 24.00 x 6.00 [610 x 610 x 152]	PDF	BP2424PCAL	$106.00	BP2424ABS	$66.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox SL Series Polycarbonate Enclosures

Opaque Door with Stainless Steel Quick-release Latch Latches, Mounting Feet

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH20164SS



Construction

- Polycarbonate
- Robotically-applied foam-in-place polyurethane seamless gasket
- 304 stainless steel cover screws
- Includes integral mounting feet
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24in·lb cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Polycarbonate with UV inhibitors hinge and latch hardware
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

c UL us CE

AttaBox SL Series Polycarbonate Enclosures – Opaque Door with Stainless Steel Quick-release Latch Latches, Mounting Feet

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AH1083SS	$125.00	10.00 x 8.00 x 3.00 [254 x 203 x 76]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH12104SS	$169.00	12.00 x 10.00 x 4.00 [305 x 254 x 102]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AH14124SS	$197.00	14.00 x 12.00 x 4.00 [356 x 305 x 102]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AH16144SS	$222.00	16.00 x 14.00 x 4.00 [406 x 356 x 102]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AH18164SS	$254.00	18.00 x 16.00 x 4.00 [457 x 406 x 102]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AH20164SS	$386.00	20.00 x 16.00 x 4.00 [508 x 406 x 102]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00
AH24246SS*	$686.00	24.00 x 24.00 x 6.00 [610 x 610 x 152]	PDF	BP2424PCAL	$106.00	BP2424ABS	$66.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox SL Series Polycarbonate Enclosures

Smoked Door with Stainless Steel Quick-release Latch Latches, Mounting Feet

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH20164CSS



Construction

- Polycarbonate
- Robotically-applied foam-in-place polyurethane seamless gasket
- 304 stainless steel cover screws
- Includes integral mounting feet
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- #10-32x5/8 cover screw size
- 20-24in·lb cover screw torque
- 1/4-20x1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Polycarbonate with UV inhibitors hinge and latch hardware
- Fully noN·metallic hinge, does not penetrate inside enclosure
- Thick, robust side wall construction eliminates side wall flexing
- Optional ABS Panel to allow unimpeded transmission of wireless signals
- Temperature Range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP66
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

c UL us CE

AttaBox SL Series Polycarbonate Enclosures – Smoked Door with Stainless Steel Quick-release Latch Latches, Mounting Feet

Part Number	Price	Enclosure Overall Size HxWxD	Drawing Link	Aluminum Subpanel	Price	ABS Subpanel	Price
AH1083CSS	$145.00	10.00 x 8.00 x 3.00 [254 x 203 x 76]	PDF	BP108AL	$22.50	BP108ABS	$21.50
AH12104CSS	$187.00	12.00 x 10.00 x 4.00 [305 x 254 x 102]	PDF	BP1210AL	$28.50	BP1210ABS	$25.50
AH14124CSS	$206.00	14.00 x 12.00 x 4.00 [356 x 305 x 102]	PDF	BP1412AL	$34.50	BP1412ABS	$29.50
AH16144CSS	$251.00	16.00 x 14.00 x 4.00 [406 x 356 x 102]	PDF	BP1614AL	$45.00	BP1614ABS	$34.00
AH18164CSS	$297.00	18.00 x 16.00 x 4.00 [457 x 406 x 102]	PDF	BP1816AL	$58.00	BP1816ABS	$45.50
AH20164CSS	$449.00	20.00 x 16.00 x 4.00 [508 x 406 x 102]	PDF	BPJ2016AL	$74.00	BP2016ABS	$60.00
AH24246CSS*	$734.00	24.00 x 24.00 x 6.00 [610 x 610 x 152]	PDF	BP2424PCAL	$106.00	BP2424ABS	$66.00

***Includes integral mounting flange**
Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].


AttaBox SL Series Polycarbonate Enclosures

Opaque Door with Mounting Feet, No Latches

STAHLIN
A ROBROY ENCLOSURES® BRAND



AH12104HW



Construction

- Polycarbonate with UV inhibitors
- Robotically-applied foam-in-place polyurethane seamless gasket
- Panel mounting capability for fixed rear panel
- Rear wall-mounting screw size #10-32x3/8
- All threaded brass inserts accept #10-32 screws
- 304 stainless steel #10-32 x 5/8 cover screws
- 20-24 in·lb cover screw torque
- 1/4-20 x 1/2 mounting feet inserts
- 10-14 in·lb mounting feet torque
- Latches omitted; requires screwdriver for entry
- Fully non-metallic hinge, does not penetrate inside enclosure
- Variable-depth side-mount capability
- Thick, robust sidewall construction eliminates sidewall flexing
- Sliding T-nut allows for infinite panel adjustment back to front
- Optional ABS panel to allow unimpeded transmission of wireless signals
- Aluminum back panel and swing-out panel mounting options
- Temperature range -40°F to +248°F [-40°C to +120°C]

Listings

- UL File No: E319779
- NEMA Ratings 1, 3R, 4, 4X, 6P, and 12 [UL508A, UL50, and UL50e]
- IEC 60529 Ratings IP68
- Flammability Rating UL94-5V
- cULus, CE, REACH
- Outdoor UV Exposure (UL 746C) (f1) Rated

AttaBox SL Series Polycarbonate Enclosures – Opaque Door with Mounting Feet, No Latches							
Part Number	*Price*	*Enclosure Overall Size HxWxD*	*Drawing Link*	*Aluminum Subpanel*	*Price*	*ABS Subpanel*	*Price*
AH1083HW	$111.00	10.00 x 8.00 x 3.00 [254 x 203 x 76]	PDF	***BP108AL***	$22.50	***BP108ABS***	$21.50
AH12104HW	$154.00	12.00 x 10.00 x 4.00 [305 x 254 x 102]	PDF	***BP1210AL***	$28.50	***BP1210ABS***	$25.50

Notes: Subpanels must be ordered separately.
Dimensions in in [mm].

Subpanels for AttaBox Series Enclosures

Aluminum Subpanels

- Material: 3003-H14 aluminum
- Finish: Mill

Aluminum Subpanels				
Part Number	**Price**	**Subpanel Size HxW**	**Fits Enclosures**	**Drawing Link**
BP66AL	$13.00	4.88 x 4.88 [124 x 124]	AH6*, AHF6*, CL7*, DS6*, DSCC60604HPL, F4PBW, J606*, JW606HPL and RJ606*	PDF
BP86AL	$15.50	6.88 x 4.88 [175 x 124]	AH86*, AHF86*, CL9*, DS806*, F6PBW, J806*, JW806*, RJ806* and RJW806HPL	PDF
BP88AL	$20.50	6.88 x 6.88 [175 x 175]	AH88*, AHF88*, DS808*, DSCC80804HPL, J8088SSH, J808*, J808W and RJ808HPL	PDF
BP108AL	$22.50	8.88 x 6.88 [226 x 175]	AH108*, AHF108*, CL11*, DS10*, DSCC1008HLL, DSW10*, F9PBW, J10*, JW10*, RJ10*, RJW1008HPL and WH-J1008HPL	PDF
BP1010AL	$28.00	8.88 x 8.88 [226 x 226]	AH1010*, AHF1010* and AHWD10106	PDF
BP1210AL	$28.50	10.88 x 8.88 [276 x 226]	AH12*, AHF12*, AHWD12106, CL13*, DS12*, DSCC121006HPL, DSW121006HPL, J1210*, JW12*, RJ12*, RJW1210HPL and WH-J1210HPL	PDF
BP1412AL	$34.50	12.88 x 10.88 [327 x 276]	AH14*, AHF14*, AHWD14126, CL15*, DS1412*, DSCC141206HPL, DSW14*, J14*, JW14*, RJ14*, RJW14* and WH-J1412HPL	PDF
BP1614AL	$45.00	14.88 x 12.88 [378 x 327]	AH16*, AHF16*, AHWD16148, DS1614*, DSCC161408HPL, DSW1614*, J16*, JW16*, RJ16*, RJW16* and WH-J1614HPL	PDF
BP1816AL	$58.00	16.88 x 14.88 [429 x 378]	AH18*, AHF18*, AHWD181610, DS18*, DSW18*, J18*, JW1816*, RJ18*, RJW18* and WH-J1816HPL	PDF
BPJ2016AL	$74.00	18.88 x 14.88 [480 x 378]	AH20*, AHF20*, AHWD20168, DS20*, J20*, JW2016HLL, RJ20* and RJW2016HPL	PDF
BP2424PCAL	$106.00	22.88 x 22.88 [581 x 581]	AH24* and AHWD242410	PDF

Note: Dimensions in inches (millimeters).



BP66AL

Aluminum Swing Panel Kits

- Material: 3003-H14 aluminum
- Finish: Mill
- Includes swing panel, (4) AHSPM brackets and mounting screws

Aluminum Swing Panel Kits				
Part Number	**Price**	**Subpanel Size HxW**	**Fits Enclosures**	**Drawing Link**
AH66SPK	$61.00	5.63 x 5.63 [143 x 143]	AH66* and AHF66*	PDF
AH86SPK	$62.00	7.63 x 5.63 [194 x 143]	AH86* and AHF86*	PDF
AH108SPK	$68.00	9.63 x 7.63 [245 x 194]	AH108* and AHF108*	PDF
AH1010SPK	$98.00	9.63 x 9.63 [245 x 245]	AH1010*, AHF1010* and AHWD10106	PDF
AH1210SPK	$73.00	11.63 x 9.63 [295 x 245]	AH12*, AHF12* and AHWD12106	PDF
AH1412SPK	$79.00	13.63 x 11.63 [346 x 295]	AH14*, AHF14* and AHWD14126	PDF
AH1614SPK	$84.00	15.63 x 13.63 [397 x 346]	AH16*, AHF16* and AHWD16148	PDF
AH1816SPK	$90.00	17.63 x 15.63 [448 x 397]	AH18*, AHF18* and AHWD181610	PDF
AH2016SPK	$140.00	19.63 x 15.63 [499 x 397]	AH20*, AHF20* and AHWD20168	PDF
AH2424SPK	$101.00	23.63 x 23.63 [600 x 600]	AH24* and AHWD242410	PDF

Note: Dimensions in inches (millimeters).
Not compatible with AttaBox SL enclosures



AH66SPK

Subpanels for AttaBox Series Enclosures

Aluminum Side Panels

- Material: 3003-H14 aluminum
- Finish: Mill

Aluminum Subpanels				
Part Number	*Price*	*Subpanel Size HxW*	*Fits Enclosures*	*Drawing Link*
SP6	$62.00	5.00 x 3.00 [127 x 76]	AH6* and AHF6*	PDF
SP8	$63.00	7.00 x 3.00 [178 x 76]	AH8* and AHF8*	PDF
SP10	$66.00	9.00 x 3.50 [229 x 89]	AH1084*, AH1086*, AH1010*, AHF1084*, AHF1086* and AHF1010*	PDF
SP12	$71.00	11.00 x 5.00 [279 x 127]	AH12106* and AHF12106*	PDF
SP14	$72.00	13.00 x 5.00 [330 x 127]	AH14126* and AHF14126*	PDF
SP16	$82.00	15.00 x 7.00 [381 x 178]	AH16148* and AHF16148*	PDF
SP18	$95.00	17.00 x 9.00 [432 x 229]	AH181610* and AHF181610*	PDF
SP20	$97.00	19.00 x 7.00 [483 x 178]	AH20168* and AHF20168*	PDF
SP24	$106.00	23.00 x 9.00 [584 x 229]	AH24*	PDF

Note: Dimensions in inches (millimeters).
Corrosion resistant slot nut fastening hardware kit included



SP8

ABS Plastic Subpanels

- Material: ABS plastic
- Finish: Mill

ABS plastic Subpanels				
Part Number	*Price*	*Subpanel Size HxW*	*Fits Enclosures*	*Drawing Link*
BP66ABS	$17.00	4.75 x 4.75 [121 x 121]	AH6*, AHF6*, CL7*, DS6*, DSCC60604HPL, F4PBW, J606*, JW606HPL and RJ606*	PDF
BP86ABS	$18.00	6.75 x 4.75 [171 x 121]	AH86*, AHF86*, CL9*, DS806*, F6PBW, J806*, JW806*, RJ806* and RJW806HPL	PDF
BP108ABS	$21.50	8.75 x 6.75 [222 x 171]	AH108*, AHF108*, CL11*, DS10*, DSCC1008HLL, DSW10*, F9PBW, J10*, JW10*, RJ10*, RJW1008HPL and WH-J1008HPL	PDF
BP1010ABS	$23.50	8.75 x 8.75 [222 x 222]	AH1010*, AHF1010* and AHWD10106	PDF
BP1210ABS	$25.50	10.75 x 8.75 [273 x 222]	AH12*, AHF12*, AHWD12106, CL13*, DS12*, DSCC121006HPL, DSW121006HPL, J1210*, JW12*, RJ12*, RJW1210HPL and WH-J1210HPL	PDF
BP1412ABS	$29.50	12.75 x 10.75 [324 x 273]	AH14*, AHF14*, AHWD14126, CL15*, DS1412*, DSCC141206HPL, DSW14*, J14*, JW14*, RJ14*, RJW14* and WH-J1412HPL	PDF
BP1614ABS	$34.00	14.75 x 12.75 [375 x 324]	AH16*, AHF16*, AHWD16148, DS1614*, DSCC161408HPL, DSW1614*, J16*, JW16*, RJ16*, RJW16* and WH-J1614HPL	PDF
BP1816ABS	$45.50	16.75 x 14.75 [425 x 375]	AH18*, AHF18*, AHWD181610, DS18*, DSW18*, J18*, JW1816*, RJ18*, RJW18* and WH-J1816HPL	PDF
BP2016ABS	$60.00	18.75 x 14.75 [476 x 375]	AH20*, AHF20*, AHWD20168, DS20*, J20*, JW2016HLL, RJ20* and RJW2016HPL	PDF
BP2424ABS	$66.00	22.75 x 22.75 [578 x 578]	AH24* and AHWD242410	PDF

Note: Dimensions in inches (millimeters).



BP108ABS

AttaBox Series Enclosure Accessories

STAHLIN
A ROBROY ENCLOSURES® BRAND

MADE IN USA

AttaBox Series – Enclosure Pole Mount Kits			
Part Number	***Price***	***For Pole Diameter***	***Fits Enclosure Width***
PM6-8	$72.00	3.00 -12.00 [76- 305]	AH66*, AH86*, AHF66*, AHF86*, AH88*, AH108*, AHF88* and AHF108*
PM10-12	$90.00		AH1010*, AH1210*, AHF1010*, AHF1210*, AHWD10106, AHWD12106, AH1412*, AHF1412* and AHWD14126
PM14-16	$96.00		AH1614*, AHF1614*, AHWD16148, AH1816*, AH2016*, AHF1816*, AHF2016*, AHWD181610 and AHWD20168
PM18-24	$112.00		AH2424* and AHWD242410
Note: Dimensions in inches [millimeters].			



PM14-16

AttaBox Series Enclosure Accessories

STAHLIN
A ROBROY ENCLOSURES® BRAND

MADE IN USA

Enclosure Latch Kits

Part Number	Price	Description
AHLKSS	$15.50	latch, replacement, quick-release, 304 stainless steel. Package of 2. For use with series enclosures.
AHLK	$13.00	latch, replacement, quick-release, polycarbonate. Package of 2. For use with series enclosures.



AHLKSS



AHLK

Accessory Kit

Part Number	Price	Description
AHAK	$15.50	mounting feet kit, polycarbonate. For use with series enclosures. Includes (4) mounting feet and mounting hardware.



AHAK

Enclosure Replacement Fasteners

Part Number	Price	Description
AHSNK	$27.00	slot nut kit, #10-32 UNF x 0.375in, Phillips pan head, zinc plated steel. Package of 2. For use with series enclosures. Includes screw and galvanized steel slot nut.
AHTSKSS	$11.00	thumb screw, replacement, #10-32 UNF x 0.375in, stainless steel. Package of 2. For use with series enclosures. Nylon washer included.
AHTSKAL	$9.25	thumb screw, replacement, #10-32 UNF x 0.375in, aluminum. Package of 2. For use with series enclosures. Nylon washer included.
RE2PKTBS	$6.25	trilobular self-tapping screw, replacement, #10-14 x 0.375in, Phillips pan head, aluminum. Package of 2. For use with series enclosures.



AHSNK



AHTSKSS



AHTSKAL



RE2PKTBS

Enclosure Swing Panel Mounts

Part Number	Price	Description
AHSPM	$37.50	Stahlin swing panel bracket, polycarbonate. Package of 4. For use with AttaBox series enclosures. Mounting screws included.



AHSPM

AttaBox Series Enclosure Accessories

STAHLIN
A ROBROY ENCLOSURES® BRAND

MADE IN USA

Mounting Flanges

Part Number	Price	Description
MFK6	$27.50	mounting flanges, replacement, polycarbonate. For use with AH66*, AH86*, AHF66* and AHF86* enclosures. Includes (2) mounting flanges and mounting hardware.
MFK8	$32.50	mounting flanges, replacement, polycarbonate. For use with AH88*, AH108*, AHF88* and AHF108* enclosures. Includes (2) mounting flanges and mounting hardware.
MFK10	$36.50	mounting flanges, replacement, polycarbonate. For use with AH1010*, AH1210*, AHF1010*, AHF1210*, AHWD10106 and AHWD12106 enclosures. Includes (2) mounting flanges and mounting hardware.
MFK12	$41.50	mounting flanges, replacement, polycarbonate. For use with AH1412*, AHF1412* and AHWD14126 enclosures. Includes (2) mounting flanges and mounting hardware.
MFK14	$45.50	mounting flanges, replacement, polycarbonate. For use with AH1614*, AHF1614* and AHWD16148 enclosures. Includes (2) mounting flanges and mounting hardware.
MFK16	$50.00	mounting flanges, replacement, polycarbonate. For use with AH1816*, AH2016*, AHF1816*, AHF2016*, AHWD181610 and AHWD20168 enclosures. Includes (2) mounting flanges and mounting hardware.



MFK6

Internal Shelf

Part Number	Price	Description
WD105	$60.00	shelf, weight distribution, 10 x 5in, aluminum. (2) screws and (2) slot nuts included.
WD106	$66.00	shelf, weight distribution, 10 x 6in, aluminum. (2) screws and (2) slot nuts included.
WD12	$71.00	shelf, weight distribution, 12 x 6in, aluminum. (2) screws and (2) slot nuts included.
WD14	$96.00	shelf, weight distribution, 14 x 6in, aluminum. (2) screws and (2) slot nuts included.
WD168	$105.00	shelf, weight distribution, 16 x 8in, aluminum. (2) screws and (2) slot nuts included.
WD1610	$129.00	shelf, weight distribution, 16 x 10in, aluminum. (2) screws and (2) slot nuts included.
WD24	$198.00	shelf, weight distribution, 24 x 10in, aluminum. (2) screws and (2) slot nuts included.



WD106

Din Rail

Part Number	Price	Length	For use with
AH6DR	$6.50	4.9in	AH6*, AH86*, AHF6* and AHF86* enclosures
AH8DR	$7.50	6.9in	AH8*, AH108*, AHF8* and AHF108* enclosures
AH10DR	$9.75	8.9in	AH10*, AH12*, AHF10*, AHF12*, AHWD10106 and AHWD12106 enclosures
AH12DR	$12.00	10.8in	AH12*, AH14*, AHF12*, AHF14* and AHWD14126 enclosures
AH14DR	$14.00	12.8in	AH14*, AH16*, AHF14*, AHF16* and AHWD16148 enclosures
AH16DR	$16.50	14.7in	AH16*, AH18*, AH20*, AHF16*, AHF18*, AHF20*, AHWD181610 and AHWD20168 enclosures
AH18DR	$18.00	16.7in	AH18* and AHF18* enclosures
AH20DR	$21.00	18.6in	AH20* and AHF20* enclosures
AH24DR	$24.50	22.5in	AH24* and AHWD242410 enclosures



AH8DR