

# BONDHUS® Wrenches

## Hex-End L-Key Sets

Bondhus hex-end L-keys are no-frills tools that get the job done right. Chamfered tool tips eliminate burrs and help the tool seat properly, while sharp corners transfer more torque to the screw to reduce stripping. Bondhus hex-end L-keys are precision machined in the USA with a proprietary high-torque steel for people who want tools that are built to last.



**Imperial** **Metric**

Hex-End L-Key Sets						
Part Number	Number of Pieces	Part Image	Overall Length	Material	Set Includes	Price
<a href="#"><u>BH22199</u></a>	22		6.8in (173mm)	Proanium high torque steel	(13) imperial long L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (9) metric long L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (2) wear-resistant tool holders	\$20.00
<a href="#"><u>BH12137</u></a>	13		6.8in (173mm)		(13) long L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (1) wear-resistant tool holder	\$10.50
<a href="#"><u>BH12199</u></a>	9		6.7in (170mm)		(9) long L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (1) wear-resistant tool holder	\$10.00
<a href="#"><u>BH12237</u></a>	13		4.3in (109mm)		(13) short L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (1) wear-resistant tool holder	\$7.00
<a href="#"><u>BH12299</u></a>	9		4.3in (109mm)		(9) short L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (1) wear-resistant tool holder	\$7.50

# BONDHUS® Wrenches

## Ball-End Hex L-Key Sets

John Bondhus invented and began manufacturing the original Balldriver® ball-end hex tool in 1964. The ball end inserts at a 25° angle, allowing for superior torque transfer and natural wrist movement so that you can work in those hard-to-reach places. Bondhus ball-end hex L-keys are precision machined in the USA with a proprietary high-torque steel for people who want tools that are built to last.



**Imperial Metric**

Ball-End Hex L-Key Sets						
Part Number	Number of Pieces	Part Image	Overall Length	Features	Set Includes	Price
<a href="#"><u>BH20199</u></a>	22		6.8in (173mm)	Ball-end tip	(13) imperial ball-end L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (9) metric ball-end L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (2) wear-resistant tool holders	\$32.00
<a href="#"><u>BH20599</u></a>	22		6.8in (173mm)	Stubby Ball-end tip	(13) imperial stubby double ball-end L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (9) metric stubby double ball-end L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (2) wear-resistant tool holders	\$39.50
<a href="#"><u>BH10937</u></a>	13		6.8in (173mm)	Ball-end tip	(13) ball-end L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (1) wear-resistant tool holder	\$18.50
<a href="#"><u>BH10999</u></a>	9		6.7in (170mm)	Ball-end tip	(9) ball-end L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (1) wear-resistant tool holder	\$15.00
<a href="#"><u>BH16537</u></a>	13		6.8in (173mm)	Stubby Ball-end tip	(13) stubby double ball-end L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (1) wear-resistant tool holder	\$22.50
<a href="#"><u>BH16599</u></a>	9		6.7in (170mm)	Stubby Ball-end tip	(9) stubby double ball-end L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (1) wear-resistant tool holder	\$18.50
<a href="#"><u>BH67037</u></a>	13		7.8in (198mm)	Stubby Double ball-end tip	(13) MaxTorque stubby ball-end L-key hex keys (0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 7/32in, 1/4in, 5/16in, 3/8in), (1) wear-resistant tool holder	\$28.50
<a href="#"><u>BH67099</u></a>	9		8.4in (213mm)	Stubby Double ball-end tip	(9) MaxTorque stubby ball-end L-key hex keys (1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm), (1) wear-resistant tool holder	\$23.00