

CEMBRE Knockout Tools

Batteries and Chargers

Keep your Cembre B-FL750NDA running through extended shifts with genuine Cembre replacement batteries and the compatible ASC55 charger. The 18 VDC lithium-ion battery platform is available in two capacities: 2.0 Ah for a lighter, more compact option and 5.2 Ah for extended runtime. These options give operators the flexibility to match battery choice to the demands of the job.




Features

- 18 VDC lithium-ion batteries for use with Cembre [B-FL750NDA](#)
- Two capacity options for lighter carry or extended runtime
- ASC55-USA/CA charger compatible with both batteries
- Charger includes 5ft 110 VAC power supply cord



ASC55-USA/CA

CB1820L

Batteries and Chargers Specifications						
Part Number	Product Image	Item	Voltage Rating	Capacity	Fits	Price
<u>ASC55-USA/CA</u>		Battery charger	—	—	Cembre CB1820L and CB1852L batteries	\$75.00
<u>CB1820L</u>		Battery	18 VDC	2.0 Ah	Cembre B-FL750NDA hydraulic punching tool	\$150.00
<u>CB1852L</u>		Battery	18 VDC	5.2 Ah	Cembre B-FL750NDA hydraulic punching tool	\$220.00

CEMBRE Knockout Tools

Overview

Cembre hydraulic knockout punching tools and accessories deliver clean, precise holes in steel, stainless steel, fiberglass, and plastic sheet materials — no grinding or deburring required. The puller-type hydraulic mechanism generates consistent force through the full punch stroke, producing smooth, burr-free results every time. The 360-degree adjustable punching head pivots 180°, giving operators confident access in tight enclosures and confined panel interiors where conventional tools cannot reach.

The Cembre punching system is fully modular. Manual and battery-powered hydraulic drivers share a common draw stud thread system, ensuring complete compatibility across the entire range of round, square, and rectangular knockout punches and dies. Round punches cover PG, ISO, trade size conduit, and metric standards from 15.5mm to 50.5mm. Square and rectangular punches are available in standard DIN sizes as well as sizes fitted to other panel components. Whether your operation involves routine panel modifications or high-volume production punching, Cembre's professional-grade punching tools deliver the long-lasting performance industrial environments demand.

Cembre Knockout Tools	
Category	Description
Hydraulic punching tools	Manual and battery-powered hydraulic drivers, 75–80 kN pulling force, 360-degree adjustable head
Round knockout punches	15.5mm to 50.5mm, covering PG, ISO, trade size conduit, and metric standards
Square knockout punches	1/16 DIN, 68x68mm, and 1/4 DIN standard panel cutouts
Rectangular knockout punches	DIN and metric dimensions for various panel components
Draw studs	7/16in and 3/4in thread sizes for use with all Cembre round punches and tools
Batteries and charger	18 VDC lithium-ion replacement batteries (2.0 Ah and 5.2 Ah) and ASC55 charger

