



Pliers & Cutting Tools

Lineman's Pliers

CHANNELLOCK® Lineman's Pliers feature Xtreme Leverage Technology (XLT™) which positions the rivet closer to the cutting edge so considerably less force is required to cut. State-of-the-art laser heat treating offers a strong and consistent pattern across the cutting edge for increased strength and longevity over traditional hardening practices. CHANNELLOCK Lineman's Pliers are forged from high-carbon U.S. steel that is specially coated for ultimate rust prevention.

Features

- Xtreme Leverage Technology (XLT™) increases performance and reduces hand fatigue
- Crosshatch teeth provide maximum grip
- Precision-machined knife and anvil style cutting edges ensure perfect mating
- Laser heat-treated cutting edges perform better and last longer



Lineman's Pliers						
Part Number	Part Image	Overall Length	Jaw Length	Jaw Capacity	Jaw Thickness	Price
<u>348</u>		8.0in [203mm]	1.74in [44.2mm]	1.50in [38.1mm]	0.43in [10.9mm]	\$37.50
<u>368</u>		8.4in [213mm]	1.41in [35.8mm]	1.50in [38.1mm]	0.55in [14.0mm]	\$37.00
<u>369</u>		9.5in [241mm]	1.54in [39.1mm]	1.50in [38.1mm]	0.55in [14.0mm]	\$33.50
<u>369CR</u>		9.5in [241mm]	1.54in [39.1mm]	1.50in [38.1mm]	0.55in [14.0mm]	\$42.00