



# Pliers & Cutting Tools

## Long Reach Pliers

CHANNELLOCK® Long Reach Pliers are specifically designed for hard-to-reach applications where standard pliers can't fit. Available in long nose with flat nose tips and crosshatch teeth for gripping, or diagonal cutting styles with laser heat-treated edges for wire cutting. Precision-machined knife and anvil style cutting edges on diagonal models ensure perfect mating for superior performance and longevity. CHANNELLOCK Long Reach Pliers are forged from high-carbon U.S. steel that is specially coated for ultimate rust prevention.

### Features

- Long nose style features flat nose tips and crosshatch teeth for gripping
- Diagonal style features laser heat-treated cutting edges for wire cutting
- Extended reach design for hard-to-access spaces
- CHANNELLOCK BLUE® grips for comfort



Long Reach Pliers							
Part Number	Part Image	Pliers Type	Overall Length	Jaw Length	Cutting	Tool Features	Price
<b>718</b>		Long Nose	7.9in [200mm]	1.18in [29.9mm]	N/A	Long reach design flat nose	\$25.50
<b>738</b>		Long Nose	7.9in [200mm]	1.18in [29.9mm]	N/A	Long reach design	\$26.50
<b>728</b>		Diagonal	7.5in [190mm]	0.91in [23.0mm]	Precision knife & anvil cutting edges	Long reach design	\$38.50
<b>758</b>		Diagonal	7.5in [190mm]	0.91in [23.0mm]	Flush cutting edges	Long reach design	\$38.00