

.3318ES1BW56C-S Cut Sheet



WEG Electric S standard efficiency AC induction motor, general purpose, 1/3hp, 1-phase, 115/208-230 VAC, 1800rpm, TEFC, NEMA 56C frame, rolled steel, C-face/rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/.3318ES1BW56C-S>

Technical Specifications

| | |
|--------------------------|---------------------|
| Brand | WEG Electric |
| Item | Motor |
| Series | S |
| Efficiency Group | Standard efficiency |
| Efficiency | 61 |
| Voltage Type | AC |
| Motor Type | Induction |
| Motor Application | General purpose |
| Horsepower Rating | 1/3hp |
| Number of Phases | 1 |
| Voltage Rating | 115/208-230 VAC |
| Synchronous Speed | 1800rpm |
| Nameplate RPM | 1735rpm |
| Overload Type | None |
| Enclosure Type | TEFC |

| | |
|---------------------------------|------------------------|
| Shaft Type | Round with square key |
| Shaft Diameter | 5/8in |
| Shaft Material | 1045 carbon steel |
| Motor Frame | NEMA 56C |
| Frame Material | Rolled steel |
| Electrically Reversible | Yes |
| Insulation Class | Class F |
| IP Rating | IP55 |
| Service Factor | 1.15 |
| Integrated Brake | No |
| NEMA Design | Design N |
| Junction Box Orientation | F1 |
| Mounting | C-face/rigid base |
| Mounting Orientation | Horizontal or vertical |

Agency Approvals

| | |
|-------------------------|--|
| UL Listed File # | E104590 |
| CE | None |
| CSA File # | LR38324 |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/.3318ES1BW56C-S.pdf>
See store item page for other formats.