

# 00518ET3E184T-S Cut Sheet



WEG Electric S premium efficiency AC induction motor, general purpose and inverter rated, 5hp, 3-phase, 208-230/460 VAC, 1800rpm, TEFC, NEMA 184T frame, rolled steel, rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/00518ET3E184T-S>

## Technical Specifications

<b>Brand</b>	WEG Electric	<b>Shaft Diameter</b>	1-1/8in
<b>Item</b>	Motor	<b>Shaft Material</b>	1045 carbon steel
<b>Series</b>	S	<b>Motor Frame</b>	NEMA 184T
<b>Efficiency Group</b>	Premium efficiency	<b>Frame Material</b>	Rolled steel
<b>Efficiency</b>	89.5	<b>Electrically Reversible</b>	Yes
<b>Voltage Type</b>	AC	<b>Insulation Class</b>	Class F
<b>Motor Type</b>	Induction	<b>IP Rating</b>	IP55
<b>Motor Application</b>	General purpose and inverter rated	<b>Constant Torque Rating</b>	4:1
<b>Horsepower Rating</b>	5hp	<b>Variable Torque Rating</b>	1000:1
<b>Number of Phases</b>	3	<b>Service Factor</b>	1.15
<b>Voltage Rating</b>	208-230/460 VAC	<b>Integrated Brake</b>	No
<b>Synchronous Speed</b>	1800rpm	<b>NEMA Design</b>	Design B
<b>Nameplate RPM</b>	1750rpm	<b>Junction Box Orientation</b>	F1
<b>Overload Type</b>	None	<b>Mounting</b>	Rigid base
<b>Enclosure Type</b>	TEFC	<b>Mounting Orientation</b>	Horizontal
<b>Shaft Type</b>	Round with square key	<b>Additional Information</b>	Class I Div 2 hazardous rating

## Agency Approvals

<b>UL Listed File #</b>	E104590
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	LR38324
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/00518ET3E184T-S.pdf>  
See store item page for other formats.