

00711 Cut Sheet



Viking step drill bit, 7/8in to 1-3/8in, size #12, 5 steps, split point, high-speed steel (HSS), gold oxide finish, 3/8in diameter 3-flat shank, 2.8in (71mm) overall length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/00711>

Technical Specifications

Brand	Viking
Item	Drill bit
Replacement	No
Drill Bit Type	Step
Size	7/8in, 1-1/8in, 1-7/32in, 1-1/4in and 1-3/8in
Step Drill Size	#12
Number Of Hole Sizes	5
Material	High-speed steel (HSS)

Finish	Gold oxide
Point Cut	Split
Shank Type	3/8in diameter 3-flat
Overall Length	2.8in (71mm)
For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Application	Hole cutting

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement