

00781 Cut Sheet



Viking step drill bit set, 4 pieces, high-speed steel (HSS), 3-flat shank, size #1, #3, #7 and #11, imperial, gold oxide finish, plastic index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/00781>

Technical Specifications

Brand	Viking	Shank Type	3-flat
Item	Drill bit set	Application	Hole cutting
Number of Pieces	4	For Use On	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
Material	High-speed steel (HSS)	Measurement Type	Imperial
Drill Bit Type	Step	Package Type	Plastic index case
Drill Bit Size	1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 7/8in and 1-1/8in	Set Includes	Includes (1) #1 13 step drill bit (1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in), (1) #3 9 step drill bit (1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in), (1) #7 11 step drill bit (1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in, 7/8in), (1) #11 2 step drill bit (7/8in, 1-1/8in), plastic carrying case
Step Drill Size	#1, #3, #7 and #11		
Number Of Hole Sizes	13, 9, 11 and 2		
Finish	Gold oxide		
Point Cut	Split		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement