

011169-00 Cut Sheet



Stego thermostat, adjustable, N.O. (close on rise) 32 to 140 deg F, 7 deg F switching differential, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011169-00>

Technical Specifications

| | |
|-----------------------------------|--|
| Brand | Stego |
| Item | Thermostat |
| IP Rating | IP20 |
| Setpoint Type | Adjustable |
| Contact 1 | N.O. (close on rise) 32 to 140 deg F |
| Switching Differential | 7 deg F |
| Switching Tolerance | +/-5.4 deg F |
| Maximum Switching Capacity | 15A resistive / 2A inductive at 120 VAC, 10A resistive / 2A inductive at 250 VAC, 30W DC |
| Connection | 2-pole terminal for 14 AWG max solid or stranded wire |
| Mounting | 35mm DIN rail |
| Application | For electrical enclosure climate control |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E164102 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |