

011169-00 Cut Sheet



Stego thermostat, adjustable, N.O. (close on rise) 32 to 140 deg F, 7 deg F switching differential, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011169-00>

Technical Specifications

Brand	Stego
Item	Thermostat
IP Rating	IP20
Setpoint Type	Adjustable
Contact 1	N.O. (close on rise) 32 to 140 deg F
Switching Differential	7 deg F
Switching Tolerance	+/-5.4 deg F
Maximum Switching Capacity	15A resistive / 2A inductive at 120 VAC, 10A resistive / 2A inductive at 250 VAC, 30W DC
Connection	2-pole terminal for 14 AWG max solid or stranded wire
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

Agency Approvals

UL Listed File #	None
UL Recognized File #	E164102
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/011169-00.pdf>
See store item page for other formats.