

011700-00 Cut Sheet



Stego mechanical thermostat, adjustable, 5 to 60 deg C, 5K switching differential, 230 VAC operating voltage, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011700-00>

Technical Specifications

Brand	Stego
Item	Mechanical thermostat
IP Rating	IP20
Setpoint Type	Adjustable
Contact 1	5 to 60 deg C
Switching Differential	5K
Switching Tolerance	-3K / +2K
Operating Voltage	230 VAC
Maximum Switching Capacity	N.C.: 10A resistive / 4A inductive, N.O.: 5A resistive / 2A inductive
Connection	4-pole terminal for 14 AWG max solid or stranded wire
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

Agency Approvals

UL Listed File #	None
UL Recognized File #	E164102
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document