

011700-01 Cut Sheet



Stego mechanical thermostat, adjustable, 40 to 140 deg F, 9 deg F switching differential, 230 VAC operating voltage, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011700-01>

Technical Specifications

Brand	Stego
Item	Mechanical thermostat
IP Rating	IP20
Setpoint Type	Adjustable
Contact 1	40 to 140 deg F
Switching Differential	9 deg F
Switching Tolerance	-5.4 deg F / +3.6 deg F
Operating Voltage	230 VAC
Maximum Switching Capacity	N.C.: 10A resistive / 4A inductive, N.O.: 5A resistive / 2A inductive
Connection	4-pole terminal for 14 AWG max solid or stranded wire
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

Agency Approvals

UL Listed File #	None
UL Recognized File #	E164102
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document