

# 011750-00 Cut Sheet



Stego thermostat, dual adjustable, N.C. (open on rise) -10 to 50 deg C, N.O. (close on rise) 20 to 80 deg C, 7K switching differential, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011750-00>

## Technical Specifications

Brand	Stego
Item	Thermostat
IP Rating	IP20
Setpoint Type	Dual adjustable
Contact 1	N.C. (open on rise) -10 to 50 deg C
Contact 2	N.O. (close on rise) 20 to 80 deg C
Switching Differential	7K
Switching Tolerance	+/-4K

Maximum Switching Capacity	15A resistive / 2A inductive at 120 VAC, N.C.: 10A resistive / 2A inductive at 250 VAC, N.O.: 5A resistive / 2A inductive at 250 VAC, 30W DC
Connection	4-pole terminal for 14 AWG max solid or 16 AWG max stranded wire
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E164102
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	215952
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/011750-00.pdf>  
See store item page for other formats.