

011900-01 Cut Sheet



Stego electronic thermostat, adjustable, 32 to 140 deg F, 5.4 deg F switching differential, 24 VDC operating voltage, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011900-01>

Technical Specifications

Brand	Stego
Item	Electronic thermostat
IP Rating	IP20
Setpoint Type	Adjustable
Contact 1	32 to 140 deg F
Switching Differential	5.4 deg F
Switching Tolerance	+/-1.8 deg F
Operating Voltage	24 VDC
Maximum Switching Capacity	16A
Connection	5-pole terminal for 14 AWG max solid or 16 AWG max stranded wire
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document