

012450-00 Cut Sheet



Stego electronic hygrometer, adjustable, 40% to 90% relative humidity, 5% RH switching differential, 230 VAC operating voltage, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/012450-00>

Technical Specifications

Brand	Stego
Item	Electronic hygrometer
IP Rating	IP20
Setpoint Type	Adjustable
Contact 1	40% to 90% relative humidity
Switching Differential	5% RH
Switching Tolerance	+/-1% at 77 deg F and 50% RH
Reaction Time	5 seconds
Operating Voltage	230 VAC
Maximum Switching Capacity	8A resistive / 1.6A inductive
Connection	5-pole terminal for 14 AWG max solid or stranded wire
Indicating Type	LED indication
Mounting	35mm DIN rail
Application	For electrical enclosure climate control

Agency Approvals

UL Listed File #	None
UL Recognized File #	E164102
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document