

01401 Cut Sheet



Viking step drill bit, 1/8in to 1/2in, size #1, 13 steps, split point, high-speed steel (HSS), gold oxide finish, 1/4in hex shank, 2.8in (71mm) overall length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/01401>

Technical Specifications

| | |
|-----------------------------|--|
| Brand | Viking |
| Item | Drill bit |
| Replacement | No |
| Drill Bit Type | Step |
| Size | 1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in and 1/2in |
| Step Drill Size | #1 |
| Number Of Hole Sizes | 13 |

| | |
|-----------------------|---|
| Material | High-speed steel (HSS) |
| Finish | Gold oxide |
| Point Cut | Split |
| Shank Type | 1/4in hex |
| Overall Length | 2.8in (71mm) |
| For Use On | Aluminum, brass, plastic, steel, bronze and cast iron |
| Application | Hole cutting |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | N/A |
| UL Recognized File # | N/A |
| UL Hazardous File # | N/A |
| CE | None |
| CSA File # | N/A |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |