

# 01402 Cut Sheet

Viking step drill bit, 3/16in to 1/2in, size #4, 6 steps, split point, high-speed steel (HSS), gold oxide finish, 1/4in hex shank, 2.5in (64mm) overall length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/01402>

## Technical Specifications

Brand	Viking	Finish	Gold oxide
Item	Drill bit	Point Cut	Split
Replacement	No	Shank Type	1/4in hex
Drill Bit Type	Step	Overall Length	2.5in (64mm)
Size	3/16in, 1/4in, 5/16in, 3/8in, 7/16in and 1/2in	For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Step Drill Size	#4	Application	Hole cutting
Number Of Hole Sizes	6		
Material	High-speed steel (HSS)		

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>