

# 01403 Cut Sheet



Viking step drill bit, 3/16in to 7/8in, size #8, 12 steps, split point, high-speed steel (HSS), gold oxide finish, 1/4in hex shank, 2.8in (71mm) overall length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/01403>

## Technical Specifications

Brand	Viking	Material	High-speed steel (HSS)
Item	Drill bit	Finish	Gold oxide
Replacement	No	Point Cut	Split
Drill Bit Type	Step	Shank Type	1/4in hex
Size	3/16in, 1/4in, 5/16in, 3/8in, 7/16in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in and 7/8in	Overall Length	2.8in (71mm)
Step Drill Size	#8	For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Number Of Hole Sizes	12	Application	Hole cutting

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>