

014112-00 Cut Sheet



Stego Smart Sensor temperature/humidity sensor, -40 to 140 deg F, 0 to 100% RH, IO-Link output, 35mm DIN rail or panel mount, M12 axial male A-coded 4-pin.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/014112-00>

Technical Specifications

| | |
|----------------------------------|-----------------------------|
| Brand | Stego |
| Item | Temperature/humidity sensor |
| Series | Smart Sensor |
| Temperature Sensing Range | -40 to 140 deg F |
| Humidity Sensing Range | 0 to 100% RH |
| Output | IO-Link |
| Operating Temperature | -40 to +176 deg F |

| | |
|-------------------------------|------------------------------|
| Operating Voltage | 24 VDC |
| Body Material | Plastic |
| IP Rating | IP20 |
| Mounting | 35mm DIN rail or panel |
| Orientation | Vertical |
| Connection | M12 axial male A-coded 4-pin |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E500143 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/014112-00.pdf>
See store item page for other formats.