

01414 Cut Sheet



Viking step drill bit, 7/8in to 1-3/8in, size #12, 5 steps, split point, high-speed steel (HSS), gold oxide finish, 1/4in hex shank, 2.8in (71mm) overall length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/01414>

Technical Specifications

Brand	Viking	Finish	Gold oxide
Item	Drill bit	Point Cut	Split
Replacement	No	Shank Type	1/4in hex
Drill Bit Type	Step	Overall Length	2.8in (71mm)
Size	7/8in, 1-1/8in, 1-7/32in, 1-1/4in and 1-3/8in	For Use On	Aluminum, brass, plastic, steel, bronze and cast iron
Step Drill Size	#12	Application	Hole cutting
Number Of Hole Sizes	5		
Material	High-speed steel (HSS)		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement