

014202-00 Cut Sheet



Stego Smart Sensor temperature/humidity sensor, -40 to 140 deg F, 0 to 100% RH, 4-20mA output, 35mm DIN rail or panel mount, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/014202-00>

Technical Specifications

Brand	Stego
Item	Temperature/humidity sensor
Series	Smart Sensor
Temperature Sensing Range	-40 to 140 deg F
Humidity Sensing Range	0 to 100% RH
Output	4-20mA
Output 2	4-20mA
Operating Temperature	-40 to +158 deg F
Operating Voltage	24 VDC
Body Material	Plastic
IP Rating	IP20
Mounting	35mm DIN rail or panel
Orientation	Vertical
Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	E500143
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document