

01461 Cut Sheet



Viking step drill bit set, 3 pieces, high-speed steel (HSS), 1/4in hex shank, size #1, #8 and #11, imperial, gold oxide finish, plastic index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/01461>

Technical Specifications

Brand	Viking	Point Cut	Split
Item	Drill bit set	Shank Type	1/4in hex
Number of Pieces	3	Application	Hole cutting
Material	High-speed steel (HSS)	For Use On	Steel, brass, plastic, stainless steel, bronze, cast iron and aluminum
Drill Bit Type	Step	Measurement Type	Imperial
Drill Bit Size	1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in, 9/16in, 5/8in, 11/16in, 3/4in, 13/16in, 7/8in and 1-1/8in	Package Type	Plastic index case
Step Drill Size	#1, #8 and #11	Set Includes	Includes (1) #1 13 step drill bit (1/8in, 5/32in, 3/16in, 7/32in, 1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 13/32in, 7/16in, 15/32in, 1/2in), (1) #11 2 step drill bit (7/8in, 1-1/8in), plastic carrying case
Number Of Hole Sizes	13, 12 and 2		
Finish	Gold oxide		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement