

0154SDSR42A-P Cut Sheet



Toshiba SD premium efficiency AC induction motor, high-performance inverter duty and severe duty, 15hp, 3-phase, 230/460 VAC, 1800rpm, TEFC, NEMA 254TC frame, cast iron, C-face/rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/0154SDSR42A-P>

Technical Specifications

Brand	Toshiba
Item	Motor
Series	SD
Efficiency Group	Premium efficiency
Efficiency	92.4
Voltage Type	AC
Motor Type	Induction
Motor Application	High-performance inverter duty and severe duty
Horsepower Rating	15hp
Number of Phases	3
Voltage Rating	230/460 VAC
Synchronous Speed	1800rpm
Nameplate RPM	1770rpm
Overload Type	None
Enclosure Type	TEFC
Shaft Type	Round with square key

Shaft Diameter	1-5/8in
Shaft Material	1045 hot rolled (C-204) steel
Motor Frame	NEMA 254TC
Frame Material	Cast iron
Electrically Reversible	Yes
Insulation Class	Class F
IP Rating	IP55
Constant Torque Rating	20:1
Variable Torque Rating	60:1
Service Factor	1.15
Integrated Brake	No
NEMA Design	Design B
Junction Box Orientation	F1
Mounting	C-face/rigid base
Mounting Orientation	Horizontal or shaft down
Additional Information	Class I Div 2 hazardous rating

Agency Approvals

UL Listed File #	E133052
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	2637147
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/0154SDSR42A-P.pdf>
See store item page for other formats.