


016100-00 Cut Sheet



Stego enclosure heater, 13W heating capacity, PTC resistor heating element, 120-240 VAC/VDC operating voltage, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/016100-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP54
Heating Capacity	13W
Heating Element	PTC resistor
Operating Voltage	120-240 VAC/VDC
Connection	(2) 22 AWG x 13in long wires
Mounting	Panel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324 & E150057
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document