


# 016250-02 Cut Sheet



Stego enclosure heater, 9W heating capacity, PTC resistor heating element, 12-24 VAC/VDC operating voltage, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/016250-02>

---

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Enclosure heater
<b>IP Rating</b>	IP54
<b>Heating Capacity</b>	9W
<b>Heating Element</b>	PTC resistor
<b>Operating Voltage</b>	12-24 VAC/VDC
<b>Connection</b>	(2) 22 AWG x 19.7in long wires
<b>Mounting</b>	Panel

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324 & E150057
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>