

01662.0-00 Cut Sheet



Stego enclosure heater, 10W heating capacity, PTC resistor heating element, 120-240 VAC/VDC operating voltage, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/01662.0-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP40
Heating Capacity	10W
Heating Element	PTC resistor
Operating Voltage	120-240 VAC/VDC
Hertz	50/60 Hz
Connection	(2) 20 AWG x 12in long wires
Mounting	Panel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/01662.0-00.pdf>
See store item page for other formats.