

018030-01 Cut Sheet



Stego Filter Fan intake fan, side mount, 202 CFM, 115 VAC operating voltage, G4 (coarse) filter mat, NEMA 12, indoor use only, 9.84 x 9.84in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018030-01>

Technical Specifications

Brand	Stego	Electrical Connection	3-pole clamp for AWG 14 wire, 7.1 in-lb maximum clamping torque
Series	Filter Fan	Maximum Static Pressure	23Pa
Airflow Direction	Intake	Operating Temperature	14 to 158 deg F
Item	Fan	Average Noise Level	56 dBA
Mounting	Side	NEMA Rating	12
With Air Flaps	No	Application	Indoor use only
Filter Media	G4 (coarse) filter mat	IP Rating	IP54 (IP55 with optional M5 filter media)
Free Airflow	202 CFM	Enclosure Cutout	9.84 x 9.84in
Airflow with Grill and Filter(s)	156 CFM	Color	RAL 7035 light gray
Operating Voltage	115 VAC	Includes	Optional mounting screws
Frequency	60 Hz	Additional Information	Purchase exhaust grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data
Power Consumption	68W		
Current Draw	800 mA		

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document