

# 018050-01 Cut Sheet



Stego Filter Fan intake fan, side mount, 372 CFM, 115 VAC operating voltage, G4 (coarse) filter mat, NEMA 12, indoor use only, 9.84 x 9.84in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018050-01>

## Technical Specifications

<b>Brand</b>	Stego
<b>Series</b>	Filter Fan
<b>Airflow Direction</b>	Intake
<b>Item</b>	Fan
<b>Mounting</b>	Side
<b>With Air Flaps</b>	No
<b>Filter Media</b>	G4 (coarse) filter mat
<b>Free Airflow</b>	372 CFM
<b>Airflow with Grill and Filter(s)</b>	203 CFM
<b>Operating Voltage</b>	115 VAC
<b>Frequency</b>	60 Hz
<b>Power Consumption</b>	85W
<b>Current Draw</b>	780 mA

<b>Electrical Connection</b>	3-pole clamp for AWG 14 wire, 7.1 in-lb maximum clamping torque
<b>Maximum Static Pressure</b>	85Pa
<b>Operating Temperature</b>	-13 to 140 deg F
<b>Average Noise Level</b>	65 dbA
<b>NEMA Rating</b>	12
<b>Application</b>	Indoor use only
<b>IP Rating</b>	IP54 (IP55 with optional M5 filter media)
<b>Enclosure Cutout</b>	9.84 x 9.84in
<b>Color</b>	RAL 7035 light gray
<b>Includes</b>	Optional mounting screws
<b>Additional Information</b>	Purchase exhaust grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>