

018210-02 Cut Sheet



Stego Filter Fan intake fan, side mount, 14 CFM, 115 VAC operating voltage, M5 (medium) filter mat, NEMA 12, safe for outdoor use, 4.92 x 4.92in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018210-02>

Technical Specifications

Brand	Stego	Electrical Connection	(2) AWG 14 x 4in long wires with cage clamps
Series	Filter Fan	Maximum Static Pressure	54Pa
Airflow Direction	Intake	Operating Temperature	14 to 158 deg F
Item	Fan	Average Noise Level	40 dBA
Mounting	Side	NEMA Rating	12
With Air Flaps	No	Application	Safe for outdoor use
Filter Media	M5 (medium) filter mat	IP Rating	IP55
Free Airflow	14 CFM	Enclosure Cutout	4.92 x 4.92in
Airflow with Grill and Filter(s)	7.1 CFM	Color	RAL 7035 light gray
Operating Voltage	115 VAC	Includes	Weather-proof UV-resistant hood and optional mounting screws
Frequency	60 Hz	Additional Information	Purchase exhaust grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data
Power Consumption	15W		
Current Draw	180 mA		

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/018210-02.pdf>
See store item page for other formats.