

018210-04 Cut Sheet



Stego Filter Fan intake fan, side mount, 12 CFM, 24 VDC operating voltage, M5 (medium) filter mat, NEMA 12, safe for outdoor use, 4.92 x 4.92in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018210-04>

Technical Specifications

Brand	Stego
Series	Filter Fan
Airflow Direction	Intake
Item	Fan
Mounting	Side
With Air Flaps	No
Filter Media	M5 (medium) filter mat
Free Airflow	12 CFM
Airflow with Grill and Filter(s)	5.9 CFM
Operating Voltage	24 VDC
Power Consumption	5W
Current Draw	210 mA

Electrical Connection	(2) AWG 14 x 4in long wires with cage clamps
Maximum Static Pressure	48Pa
Operating Temperature	14 to 158 deg F
Average Noise Level	40 dBA
NEMA Rating	12
Application	Safe for outdoor use
IP Rating	IP55
Enclosure Cutout	4.92 x 4.92in
Color	RAL 7035 light gray
Includes	Weather-proof UV-resistant hood and optional mounting screws
Additional Information	Purchase exhaust grille separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document