

# 018210-04 Cut Sheet



Stego Filter Fan intake fan, side mount, 12 CFM, 24 VDC operating voltage, M5 (medium) filter mat, NEMA 12, safe for outdoor use, 4.92 x 4.92in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018210-04>

## Technical Specifications

<b>Brand</b>	Stego
<b>Series</b>	Filter Fan
<b>Airflow Direction</b>	Intake
<b>Item</b>	Fan
<b>Mounting</b>	Side
<b>With Air Flaps</b>	No
<b>Filter Media</b>	M5 (medium) filter mat
<b>Free Airflow</b>	12 CFM
<b>Airflow with Grill and Filter(s)</b>	5.9 CFM
<b>Operating Voltage</b>	24 VDC
<b>Power Consumption</b>	5W
<b>Current Draw</b>	210 mA

<b>Electrical Connection</b>	(2) AWG 14 x 4in long wires with cage clamps
<b>Maximum Static Pressure</b>	48Pa
<b>Operating Temperature</b>	14 to 158 deg F
<b>Average Noise Level</b>	40 dBA
<b>NEMA Rating</b>	12
<b>Application</b>	Safe for outdoor use
<b>IP Rating</b>	IP55
<b>Enclosure Cutout</b>	4.92 x 4.92in
<b>Color</b>	RAL 7035 light gray
<b>Includes</b>	Weather-proof UV-resistant hood and optional mounting screws
<b>Additional Information</b>	Purchase exhaust grille separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/018210-04.pdf>  
See store item page for other formats.