

# 018600-04 Cut Sheet



Stego exhaust fan, top mount, 203 CFM, 24 VDC operating voltage, G3 (coarse) filter mat, NEMA 3R, indoor use only, 9.69 x 9.69in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018600-04>

## Technical Specifications

<b>Brand</b>	Stego
<b>Airflow Direction</b>	Exhaust
<b>Item</b>	Fan
<b>Mounting</b>	Top
<b>With Air Flaps</b>	No
<b>Filter Media</b>	G3 (coarse) filter mat
<b>Free Airflow</b>	203 CFM
<b>Operating Voltage</b>	24 VDC
<b>Power Consumption</b>	20W
<b>Electrical Connection</b>	2-pole clamp for AWG 14 wire, 7.1 in-lb maximum clamping torque
<b>NEMA Rating</b>	3R
<b>Application</b>	Indoor use only
<b>IP Rating</b>	IP32
<b>Enclosure Cutout</b>	9.69 x 9.69in
<b>Color</b>	RAL 7035 light gray
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Purchase intake grille separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>