

018710-30 Cut Sheet



Stego Filter Fan Plus FPI intake fan, side mount, 31 CFM, 230 VAC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 4.88 x 4.88in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018710-30>

Technical Specifications

Brand	Stego	Electrical Connection	(2) AWG 22 x 11.8in long wires
Series	Filter Fan Plus FPI	Maximum Static Pressure	64Pa
Airflow Direction	Intake	Operating Temperature	-4 to 158 deg F
Item	Fan	Average Noise Level	49 dBA
Mounting	Side	NEMA Rating	12
With Air Flaps	No	Application	Indoor use only
Filter Media	G3 (coarse) filter mat	IP Rating	IP54
Free Airflow	31 CFM	Enclosure Cutout	4.88 x 4.88in
Airflow with Grill and Filter(s)	25 CFM	Color	RAL 7035 light gray
Operating Voltage	230 VAC	Includes	Optional mounting screws
Frequency	60 Hz	Additional Information	Purchase exhaust grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data
Power Consumption	19W		
Current Draw	83 mA		

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document