

018723-30 Cut Sheet



Stego Filter Fan Plus FPI intake fan, side mount, 106 CFM, 12 VDC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 6.93 x 6.93in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018723-30>

Technical Specifications

| | |
|---|------------------------|
| Brand | Stego |
| Series | Filter Fan Plus FPI |
| Airflow Direction | Intake |
| Item | Fan |
| Mounting | Side |
| With Air Flaps | No |
| Filter Media | G3 (coarse) filter mat |
| Free Airflow | 106 CFM |
| Airflow with Grill and Filter(s) | 88 CFM |
| Operating Voltage | 12 VDC |
| Power Consumption | 12W |
| Current Draw | 1000 mA |

| | |
|--------------------------------|---|
| Electrical Connection | 3-pole clamp for AWG 14 wire, 7.1 in-lb maximum clamping torque |
| Maximum Static Pressure | 127Pa |
| Operating Temperature | -13 to 158 deg F |
| Average Noise Level | 53 dBA |
| NEMA Rating | 12 |
| Application | Indoor use only |
| IP Rating | IP54 |
| Enclosure Cutout | 6.93 x 6.93in |
| Color | RAL 7035 light gray |
| Includes | Optional mounting screws |
| Additional Information | Purchase exhaust grille separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E234324 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/018723-30.pdf>
See store item page for other formats.