

018800-00 Cut Sheet



Stego Filter Fan Plus FPO exhaust fan, side mount, 14 CFM, 230 VAC operating voltage, with air flaps, NEMA 12, indoor use only, 3.62 x 3.62in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018800-00>

Technical Specifications

Brand	Stego	Electrical Connection	(2) AWG 22 x 11.8in long wires
Series	Filter Fan Plus FPO	Maximum Static Pressure	42Pa
Airflow Direction	Exhaust	Operating Temperature	-4 to 158 deg F
Item	Fan	Average Noise Level	38 dBA
Mounting	Side	NEMA Rating	12
With Air Flaps	Yes	Application	Indoor use only
Free Airflow	14 CFM	IP Rating	IP54
Airflow with Grill and Filter(s)	8.8 CFM	Enclosure Cutout	3.62 x 3.62in
Operating Voltage	230 VAC	Color	RAL 7035 light gray
Frequency	60 Hz	Includes	Optional mounting screws
Power Consumption	12W	Additional Information	Purchase intake grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data
Current Draw	52 mA		

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document