

018800-40 Cut Sheet



Stego Filter Fan Plus FPO exhaust fan, side mount, 11 CFM, 230 VAC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 3.62 x 3.62in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018800-40>

Technical Specifications

Brand	Stego
Series	Filter Fan Plus FPO
Airflow Direction	Exhaust
Item	Fan
Mounting	Side
With Air Flaps	No
Filter Media	G3 (coarse) filter mat
Free Airflow	11 CFM
Airflow with Grill and Filter(s)	7.4 CFM
Operating Voltage	230 VAC
Frequency	60 Hz
Power Consumption	12W
Current Draw	52 mA

Electrical Connection	(2) AWG 22 x 11.8in long wires
Maximum Static Pressure	42Pa
Operating Temperature	-4 to 158 deg F
Average Noise Level	36 dBA
NEMA Rating	12
Application	Indoor use only
IP Rating	IP54
Enclosure Cutout	3.62 x 3.62in
Color	RAL 7035 light gray
Includes	Optional mounting screws
Additional Information	Purchase intake grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/018800-40.pdf>
See store item page for other formats.