

018801-00 Cut Sheet



Stego Filter Fan Plus FPO exhaust fan, side mount, 19 CFM, 48 VDC operating voltage, with air flaps, NEMA 12, indoor use only, 3.62 x 3.62in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018801-00>

Technical Specifications

| | |
|---|---------------------|
| Brand | Stego |
| Series | Filter Fan Plus FPO |
| Airflow Direction | Exhaust |
| Item | Fan |
| Mounting | Side |
| With Air Flaps | Yes |
| Free Airflow | 19 CFM |
| Airflow with Grill and Filter(s) | 11 CFM |
| Operating Voltage | 48 VDC |
| Power Consumption | 3W |
| Current Draw | 63 mA |

| | |
|--------------------------------|-----------------------------------|
| Electrical Connection | (2) AWG 22 x 11.8in long wires |
| Maximum Static Pressure | 41Pa |
| Operating Temperature | -4 to 158 deg F |
| Average Noise Level | 49 dBA |
| NEMA Rating | 12 |
| Application | Indoor use only |
| IP Rating | IP54 |
| Enclosure Cutout | 3.62 x 3.62in |
| Color | RAL 7035 light gray |
| Includes | Optional mounting screws |
| Additional Information | Purchase intake grille separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E234324 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/018801-00.pdf>
See store item page for other formats.