

018823-00 Cut Sheet



Stego Filter Fan Plus FPO exhaust fan, side mount, 164 CFM, 12 VDC operating voltage, with air flaps, NEMA 12, indoor use only, 6.93 x 6.93in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018823-00>

Technical Specifications

Brand	Stego	Electrical Connection	3-pole clamp for AWG 14 wire, 7.1 in-lb maximum clamping torque
Series	Filter Fan Plus FPO	Maximum Static Pressure	150Pa
Airflow Direction	Exhaust	Operating Temperature	-13 to 158 deg F
Item	Fan	Average Noise Level	53 dBA
Mounting	Side	NEMA Rating	12
With Air Flaps	Yes	Application	Indoor use only
Free Airflow	164 CFM	IP Rating	IP54
Airflow with Grill and Filter(s)	82 CFM	Enclosure Cutout	6.93 x 6.93in
Operating Voltage	12 VDC	Color	RAL 7035 light gray
Power Consumption	12W	Includes	Optional mounting screws
Current Draw	1000 mA	Additional Information	Purchase intake grille separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/018823-00.pdf>
See store item page for other formats.