

018849-00 Cut Sheet



Stego Filter Fan Plus FPO exhaust fan, side mount, 414 CFM, 115 VAC operating voltage, with air flaps, NEMA 12, indoor use only, 11.46 x 11.46in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018849-00>

Technical Specifications

Brand	Stego
Series	Filter Fan Plus FPO
Airflow Direction	Exhaust
Item	Fan
Mounting	Side
With Air Flaps	Yes
Free Airflow	414 CFM
Airflow with Grill and Filter(s)	230 CFM
Operating Voltage	115 VAC
Frequency	60 Hz
Power Consumption	90W
Current Draw	783 mA
Electrical Connection	3-pole clamp for AWG 14 wire, 7.1 in-lb maximum clamping torque

Maximum Static Pressure	80Pa
Operating Temperature	-13 to 95 deg F
Average Noise Level	62 dBA
NEMA Rating	12
Application	Indoor use only
IP Rating	IP54
Enclosure Cutout	11.46 x 11.46in
Color	RAL 7035 light gray
Includes	Optional mounting screws
Additional Information	Purchase intake grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/018849-00.pdf>
See store item page for other formats.