

019250-01 Cut Sheet



Stego StegoJet series compact directional cooling fan, for precise cooling of heat sources inside an enclosure, 100-240 VAC operating voltage, 50/60 Hz, panel mount, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/019250-01>

Technical Specifications

Brand	Stego
Item	Compact directional cooling fan
Series	StegoJet
Application	For precise cooling of heat sources inside an enclosure
Operating Voltage	100-240 VAC
Hertz	50/60 Hz
Mounting	Panel
IP Rating	IP20

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document