

019310-00 Cut Sheet



Stego fan tray, rack mount, 339 CFM, 115 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/019310-00>

Technical Specifications

Brand	Stego
Item	Fan tray
Mounting	Rack
Free Airflow	339 CFM
Operating Voltage	115 VAC
Frequency	60 Hz
Power Consumption	45W
Operating Temperature	14 to 140 deg F
Average Noise Level	55 dBA
IP Rating	IP20
Includes	Optical indicator in front panel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/019310-00.pdf>
See store item page for other formats.