

# 019510-00 Cut Sheet



Stego fan tray, rack mount, 1016 CFM, 115 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/019510-00>

## Technical Specifications

Brand	Stego
Item	Fan tray
Mounting	Rack
Free Airflow	1016 CFM
Operating Voltage	115 VAC
Frequency	60 Hz
Power Consumption	135W
Operating Temperature	14 to 140 deg F
Average Noise Level	58 dBA
IP Rating	IP20
Includes	Optical indicator in front panel

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/019510-00.pdf>  
See store item page for other formats.