

# 019510-00 Cut Sheet



Stego fan tray, rack mount, 1016 CFM, 115 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/019510-00>

---

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Fan tray
<b>Mounting</b>	Rack
<b>Free Airflow</b>	1016 CFM
<b>Operating Voltage</b>	115 VAC
<b>Frequency</b>	60 Hz
<b>Power Consumption</b>	135W
<b>Operating Temperature</b>	14 to 140 deg F
<b>Average Noise Level</b>	58 dBA
<b>IP Rating</b>	IP20
<b>Includes</b>	Optical indicator in front panel

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>