

020320-00 Cut Sheet



Stego enclosure heater, hazardous location rated, 100W heating capacity, high performance cartridge heating element, 230 VAC operating voltage, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/020320-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
Environmental Requirements	Hazardous location rated
IP Rating	IP66
Heating Capacity	100W
Heating Element	High performance cartridge
Operating Voltage	230 VAC
Connection	3.3ft silicone cable with (3) 18 AWG conductors
Mounting	35mm DIN rail

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document