

# 020340-00 Cut Sheet



Stego enclosure heater, hazardous location rated, 200W heating capacity, high performance cartridge heating element, 230 VAC operating voltage, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/020340-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Enclosure heater
<b>Environmental Requirements</b>	Hazardous location rated
<b>IP Rating</b>	IP66
<b>Heating Capacity</b>	200W
<b>Heating Element</b>	High performance cartridge
<b>Operating Voltage</b>	230 VAC
<b>Connection</b>	3.3ft silicone cable with (3) 18 AWG conductors
<b>Mounting</b>	35mm DIN rail

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>