

# 021200-30 Cut Sheet



Stego Varioline LED enclosure light, 100-240 VAC operating voltage, no switch, 15.6in length, 1080 Lm, magnet mount, 2-pole plug with snap lock, 11W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/021200-30>

## Technical Specifications

Brand	Stego
Item	LED enclosure light
Series	Varioline
Operating Voltage	100-240 VAC
Switch Type	None
Length	15.6in
Luminous Flux	1080 Lm
Integral Receptacle	No
Mounting	Magnet
Connection	2-pole plug with snap lock
Power Consumption	11W
IP Rating	IP20
Requires	M5 mounting screws and power or extension cable

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/021200-30.pdf>  
See store item page for other formats.