

022000-00 Cut Sheet



Stego Varioline LED enclosure light, 100-240 VAC operating voltage, on/off switch, 23.4in length, 1730 Lm, screw mount, 2-pole plug with snap lock, 16W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/022000-00>

Technical Specifications

Brand	Stego
Item	LED enclosure light
Series	Varioline
Operating Voltage	100-240 VAC
Switch Type	On/off
Length	23.4in
Luminous Flux	1730 Lm
Integral Receptacle	No
Mounting	Screw
Connection	2-pole plug with snap lock
Power Consumption	16W
IP Rating	IP20
Requires	Power or extension cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/022000-00.pdf>
See store item page for other formats.