

022000-30 Cut Sheet



Stego Varioline LED enclosure light, 100-240 VAC operating voltage, on/off switch, 23.4in length, 1730 Lm, magnet mount, 2-pole plug with snap lock, 16W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/022000-30>

Technical Specifications

| | |
|----------------------------|-------------------------------------------------|
| Brand | Stego |
| Item | LED enclosure light |
| Series | Varioline |
| Operating Voltage | 100-240 VAC |
| Switch Type | On/off |
| Length | 23.4in |
| Luminous Flux | 1730 Lm |
| Integral Receptacle | No |
| Mounting | Magnet |
| Connection | 2-pole plug with snap lock |
| Power Consumption | 16W |
| IP Rating | IP20 |
| Requires | M5 mounting screws and power or extension cable |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | E234324 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |