

022100-00 Cut Sheet



Stego Varioline LED enclosure light, 100–240 VAC operating voltage, motion sensor switch, 23.4in length, 1730 lm, screw mount, 2-pole plug with snap lock, 16W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/022100-00>

Technical Specifications

Brand	Stego
Item	LED enclosure light
Series	Varioline
Operating Voltage	100–240 VAC
Switch Type	Motion sensor
Length	23.4in
Luminous Flux	1730 lm
Color Temperature	6500K

Beam Angle	120 degrees
Integral Receptacle	No
Mounting	Screw
Connection	2-pole plug with snap lock
Power Consumption	16W
IP Rating	IP20
Rotatable	Yes
Requires	Power or extension cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/022100-00.pdf>
See store item page for other formats.